



CARTRIDGE

Model: 2030 LD P3 R
P/N 113930000

Particle filter with special snap-in connector for dusts, fumes, mists.

The cartridge shall be used in pairs with half masks **DUETTA** and **DUO** or full face masks type **TR 2002 CL2** and **TR 2002 CL3** with **DUPLA** adapter.



TECHNICAL DATA

Inhalation resistance
at 15 l/min: 0.4 mbar
at 47.5 l/min: 1.3 mbar

Particle filtration performance - Long duration

Filter Type	Class	Testing Flow (l/min)	Testing Aerosol	Penetration Max required (%)	Penetration Max measured (%)		
					(1)	(2)	(3)
P R	3	47.5	NaCl	0.05	0.003	/	/
			Paraffin Oil	0.05	0.002	0.001	0.001

(1) 3 min exposure

(2) after exposure at 60 mg of paraffin oil

(3) 3 min exposure after (2) and after 24h storage

Marking R means that the filter is reusable for more than one workshift.

Limitations for use

Do not use in areas where the oxygen concentration is lower than 17% nor in presence of gases and vapours.

CLASSIFICATION

Filter complying with the provisions of Regulation (EU) **2016/425**.

Particle Cartridge / Filter, class P3 R, to EN143:2000 / A1:2006.

Label colour code: white.

MARKING





CARTRIDGE

Model: 2030 LD P3 R
P/N 113930000

MATERIALS

Housing: polypropylene
Filter Media: filter paper

STORAGE

Store at temperatures between -20 and +50 °C and RH <80%

WEIGHT

60 g (2.12 oz) approximately

DIMENSIONS / PACKING

Cartridge is sold in 4 piece boxes with dimensions 175 x 115 x 90 mm

SHELF LIFE

Filters duly stored and in their original packaging will last ten years from production. The expiry date is printed onto filter label and packaging.

For more information please check the notes along with the products or the ones published on the website: www.spasciani.com

NOTE: SPASCIANI SpA does not take any responsibility for any possible and unintentional mistake and reserve the faculty of modify materials and technical characteristics of its products at any time and without any notice. The pictures are purely indicative and may not represent the actual product described in the text.